

## Liquid Flux Rosin Mildly Activated (RMA) in 6ml (0.2oz) Refillable Pen with Tip + Brush

### Product Highlights

High Solids Content  
No-Clean  
Alcohol-Based  
Ideal for all rework, solder, and de-solder applications  
Excellent wetting  
Easily cleaned with water or isopropyl alcohol (IPA)  
Can be used with Leaded and Lead-Free applications  
**RoHS 3 and REACH compliant**



### Specifications

Flux Type:	RMA Liquid (for Leaded and Lead-Free applications)
Flux Classification:	ROL1
Specific Gravity:	0.9
Packaging:	Refillable Pen 6ml (0.2oz) - Two Ends: Tip and Brush
Shelf Life:	Refrigerated >24 months, Unrefrigerated >24 months

### Dispensing

Gently press tip into work piece (depress tip) to dispense.

### Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). The liquid flux can be allowed to freeze. Freezing will not degrade this product. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

### Transportation

This product requires ground shipping. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground will not impact this product's stated shelf life.

### Cleaning

This is a water-soluble liquid flux; post-use cleaning is required. Clean with water or isopropyl alcohol (IPA).

### Conforms to the following Industry Standards:

J-STD-004B, Amendment 1 (Solder Fluxes):	Yes
RoHS 3 Directive 2015/863/EU:	Yes