

# 842AR-P Pen



## Silver Conductive Pen

842AR-P pen dispenses an acrylic lacquer pigmented with highly conductive silver flakes. The cured traces are durable and corrosion resistant. They adhere well to plastics and most electronic substrates. The traces are flexible, but the product works best on a smooth, flat, hard surface. The valve tip opens when pressed against the surface, and the flow is controlled by squeezing the barrel.

This pen repairs damaged traces on keyboards, game controllers, remote controls, mixing boards, and PCBs. It also creates conductive traces for prototyping, hobbies, or maker projects. It is great for making small connections in or between circuits, such as jumpers, through-holes, bridges, and links. It can also be used to increase the surface area of contacts by painting the area around them.

For applications where high conductivity is not required, the 838AR-P Carbon Conductive Pen and the 841AR-P Nickel Conductive Pen provide economical alternatives.



## Features and Benefits

- Creates durable, reliable and conductive traces
- Typical trace width: 1.5–2.0 mm
- Dries in 1 minute at room temperature
- Typical linear resistance: 0.3–0.8  $\Omega$ /cm
- Good flexibility
- Strong corrosion resistance
- Does not contain toluene, xylene, or MEK

## Available Packaging

Cat. No.	Packaging	Net Vol.	Net Wt.
842AR-P	Pen	5 mL	9.14 g

## Contact Information

MG Chemicals, 1210 Corporate Drive  
Burlington, Ontario, Canada L7L 5R6

Email: [support@mgchemicals.com](mailto:support@mgchemicals.com)

Phone: North America: +(1)800-340-0772

International: +(1) 905-331-1396

Europe: +(44)1663 362888

## Cured Properties

Resistivity	1 x 10 <sup>-4</sup> $\Omega$ ·cm
Service Temperature Range	-40–120 °C

## Usage Parameters

Dry To Touch	1 min
Cure Times	24 h @ 22 °C 30 min @ 65 °C
Approximate Linear Coverage	50 m

## Uncured Properties

Viscosity @ 25 °C	1 060 cP
Density	1.83 g/mL
Percent Solids	58 %
Shelf Life	3 y
Calculated VOC	200 g/L

# 842AR-P Pen



## Safety Data Sheet

Read the product SDS before using this product (downloadable at [www.mgchemicals.com](http://www.mgchemicals.com)).

## Recommended Preparation

Clean the substrate with Isopropyl Alcohol, MG #824, so the surface is free of oils, dust, and other residues.

## Application Instructions

1. Shake pen vigorously until the ball moves freely inside.
2. Hold pen at angle and depress tip against surface.
3. Draw pen across surface while gently squeezing barrel.
4. Let dry 1 min before handling or heat cure.
5. Clean tip, replace cap and store tip up after use.

## Cure Instructions

Allow to dry at room temperature for 24 hours, or after letting sit for 1 minute, cure the coating in an oven for 30 minutes @ 65 °C.

## Storage and Handling

Store between -5 and 22 °C in a dry area, away from sunlight (see SDS).

## Disclaimer

This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.